



B2F13D50G130TN Flexible Copper Braid

By Burndy
Catalog # [B2F13D50G130TN](#)

Tin Plated Ferrules.



General

Catalog Number	B2F13D50G130TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810506493

Dimensions

Dimension - L Length Overall mm	343
Dimension - Length Overall inch	13.5
Length	13.5 in

Electrical Ratings

Rating - Indoor Amperage	600 A
Rating - Outdoor Amperage	720 A

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	6
-----------------------	---

Product Assets

- [3D Models - B2F13D50G130TN_MODEL-PDF](#)
- [3D Models - B2F13D50G130TN_MODEL-STEP](#)
- [3D Models - B2F13D50G130TN_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30004626](#)
- [Specifications - B2F13D50G130TN](#)