



B2F13D50G130TN Flexible Copper Braid

By Burndy
Catalog # B2F13D50G130TN

Tin Plated Ferrules.

Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	B2F13D50G130TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810506493

Dimensions

Dimension - L Length Overall mm	343
---------------------------------	-----



Dimension - Length Overall inch	13.5
Length	13.5 in

Electrical Ratings

Rating - Indoor Amperage	600 A
Rating - Outdoor Amperage	720 A

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	6
-----------------------	---

Product Assets

- [3D Models - B2F13D50G130TN_MODEL-IGES](#)
- [3D Models - B2F13D50G130TN_MODEL-PDF](#)
- [3D Models - B2F13D50G130TN_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30004626](#)
- [Specifications - B2F13D50G130TN](#)