



## B2F16G127 Flexible Copper Braid

By Burndy  
Catalog # [B2F16G127](#)

Flexible Copper Braid.



### General

Catalog Number	B2F16G127
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
UPC	781810417935

### Dimensions

Dimension - L Length Overall mm	406 mm
Dimension - Length Overall inch	16.00 in
Length	16 in

### Electrical Ratings

Rating - Indoor Amperage	600 A
Rating - Outdoor Amperage	720 A

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	840

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 10059191-01\\_A](#)  
[Specifications - B2F16G127](#)