



B2F21G118TN Flexible Copper Braid

By Burndy

Catalog # [B2F21G118TN](#)

Tin Plated Ferrules.



General

Catalog Number	B2F21G118TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810135914
UPC 12 Digit	7818101359144

Dimensions

Dimension - L Length Overall mm	533 mm
Dimension - Length Overall inch	21.00 in
Length	21 in

Electrical Ratings

Rating - Indoor Amperage	600
Rating - Outdoor Amperage	720

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - B2F21G118TN](#)