



## B2F26NX90TN Flexible Copper Braid

By Burndy  
Catalog # [B2F26NX90TN](#)

Tin Plated Ferrules.



### General

Catalog Number	B2F26NX90TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810200193
UPC 12 Digit	7818102001933

### Dimensions

Dimension - Hole Size inch	0.54 in
Dimension - L Length Overall mm	660 mm
Dimension - Length Overall inch	26.00 in
Length	26 in
Thickness - Pad	0.38 in

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Carton Quantity	8
Minimum Pack Quantity	1
Pallet Quantity	320

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50115830](#)  
[Specifications - B2F26NX90TN](#)