



B2G10G146SV Flexible Copper Braid

By Burndy
Catalog # B2G10G146SV

Silver Plated Ferrules.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	B2G10G146SV
Connector Type	Braid
Material	Copper
Material - Ferrules	Silver Plated Copper Ferrule
Physical Attribute - Number of Braids	2
Plated	Y
UPC	621945447912

Dimensions

Dimension - L Length Overall	254
mm	
Dimension - Length Overall	10
inch	
Length	10 in
Weight	2.95 lb

Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	900

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50061158](#)
- [Specifications - B2G10G146SV](#)