



B2G12D75G70SV Flexible Copper Braid

By Burndy
Catalog # [B2G12D75G70SV](#)

Silver Plated Ferrules.



General

Catalog Number	B2G12D75G70SV
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810076712

Dimensions

Dimension - L Length Overall mm	324 mm
Dimension - Length Overall inch	12.75 in
Length	12.75 in

Electrical Ratings

Rating - Indoor Amperage	700
Rating - Outdoor Amperage	840

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10031575-01](#)
[Specifications - B2G12D75G70SV](#)