



## B2G12NSV Flexible Copper Braid

By Burndy  
Catalog # [B2G12NSV](#)

Silver Plated Ferrules.



### General

|                                       |              |
|---------------------------------------|--------------|
| Catalog Number                        | B2G12NSV     |
| Connector Type                        | Braid        |
| Material                              | Copper       |
| Material - Ferrules                   | Y            |
| Physical Attribute - Number of Braids | 2            |
| Plated                                | Y            |
| UPC                                   | 781810078204 |

### Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 305 mm   |
| Dimension - Length Overall inch | 12.00 in |
| Length                          | 12 in    |

### Electrical Ratings

|                           |       |
|---------------------------|-------|
| Rating - Indoor Amperage  | 700 A |
| Rating - Outdoor Amperage | 840 A |

### Certifications And Compliance

|                                    |       |
|------------------------------------|-------|
| Certification - CSA Approved       | No    |
| Certification - ETL                | No    |
| Certification - UL Recognized      | No    |
| Certification - cULus              | No    |
| Industry Standard(s)               | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX    |
| UL Listed                          | Yes   |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 8 |
|-----------------------|---|

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 30015322](#)  
[Specifications - B2G12NSV](#)