

B2G16N Flexible Copper Braid

By Burndy
Catalog # B2G16N

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

| | |
|---------------------------------------|--------------|
| Catalog Number | B2G16N |
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 2 |
| Plated | Y |
| UPC | 781810049532 |

Dimensions

| | |
|------------------------------|--------|
| Dimension - L Length Overall | 406 mm |
| mm | |

| | |
|----------------------------|----------|
| Dimension - Length Overall | 16.00 in |
| inch | |
| Length | 16 in |

Electrical Ratings

| | |
|---------------------------|-------|
| Rating - Indoor Amperage | 700 A |
| Rating - Outdoor Amperage | 840 A |

Certifications And Compliance

| | |
|--------------------------------|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards | UL467 |
| Met | |
| Standards - RoHS Compliance | EX |
| Status | |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 30015322](#)
[Specifications - B2G16N](#)