



## B2G16NSV Flexible Copper Braid

By Burndy  
Catalog # [B2G16NSV](#)

Silver Plated Ferrules.



### General

Catalog Number	B2G16NSV
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	621945455719

### Dimensions

Dimension - L Length Overall mm	406 mm
Dimension - Length Overall inch	16.00 in
Length	16 in

### Electrical Ratings

Rating - Indoor Amperage	700 A
Rating - Outdoor Amperage	840 A

### Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	960

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30015322](#)
- [Specifications - B2G16NSV](#)