



## B2G28N Flexible Copper Braid

By Burndy  
Catalog # [B2G28N](#)

Flexible Copper Braid.



### General

Catalog Number	B2G28N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
UPC	781810207048

### Dimensions

Dimension - L Length Overall mm	711 mm
Dimension - Length Overall inch	28.00 in
Length	28 in

### Electrical Ratings

Rating - Indoor Amperage	840 A
Rating - Outdoor Amperage	700 A

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Carton Quantity	8
Minimum Pack Quantity	1
Pallet Quantity	720

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30015322](#)
- [Specifications - B2G28N](#)