



# B2G30D81TNCG1 Flexible Copper Braid

By Burndy  
Catalog # [B2G30D81TNCG1](#)

Tin Plated Ferrules.



## General

Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810420751
UPC 12 Digit	7818104207511

## Dimensions

Dimension - L Length Overall mm	222 mm
Dimension - Length Overall inch	8.75 in
Length	30.81 in
Weight	7.8 lb

## Electrical Ratings

Rating - Outdoor Amperage	700
---------------------------	-----

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	2
Minimum Pack Quantity	1
Pallet Quantity	70

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50115834](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-B2G30D81TNCG1-SPEC-EN | REV 1/2024