



B32F32G20TN Flexible Copper Braid

By Burndy
Catalog # [B32F32G20TN](#)

Tin Plated Ferrules.



General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	6
Plated	Y
UPC	621945454576

Dimensions

Dimension - L Length Overall mm	813
Dimension - Length Overall inch	32
Length	32 in

Electrical Ratings

Amperage Rating	1500 A
-----------------	--------

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	150

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50064228](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-B32F32G20TN-SPEC-EN | REV 5/2024