



## B33F14D63G9TN Flexible Copper Braid

By Burndy  
Catalog # B33F14D63G9TN

Tin Plated Copper Braid 140625X3.5X0.68.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	B33F14D63G9TN
Connector Type	Braid
Material	Copper
Plated	y
Plating Type	Tin Plated
UPC	621945452718
UPC 12 Digit	6219454527188

### Dimensions

Length	14.63 in
Weight	8.9 lb

### Electrical Ratings

Current Rating	2100 A
----------------	--------

### Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	

### Logistics

Carton Quantity	2
Minimum Pack Quantity	1
Pallet Quantity	234

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50063914](#)
- [Specifications - B33F14D63G9TN](#)