

## B33F24N Flexible Copper Braid

By Burndy  
Catalog # B33F24N

Flexible Tinned Copper Braid 24 X 3 X 0.62.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	B33F24N
Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	9
UPC	781810551066
UPC 12 Digit	7818105510666

### Dimensions

Dimension - L Length Overall mm	610
Dimension - Length Overall inch	24
Dimension - Width inch	3
Dimension - Width mm	76 mm
Length	24 in

### Electrical Ratings

Amperage Rating	2000 A
-----------------	--------

### Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	540

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50005747](#)  
[Specifications - B33F24N](#)