



B33G12G43 Flexible Copper Braid

By Burndy
Catalog # [B33G12G43](#)

Flexible Copper Braid.



General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	9
Plated	Y
UPC	781810567869

Dimensions

Dimension - L Length Overall mm	305
Dimension - Length Overall inch	12
Length	12 in

Electrical Ratings

Amperage Rating	3000 A
-----------------	--------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50009724](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-B33G12G43-SPEC-EN | REV 1/2024