



B33G394NTN Flexible Copper Braid

By Burndy

Catalog # [B33G394NTN](#)

Tin Plated Ferrules.



General

Catalog Number	B33G394NTN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	3
Plated	Y
UPC	781810427309
UPC 12 Digit	7818104273099

Dimensions

Dimension - L Length Overall mm	991 mm
Dimension - Length Overall inch	39.00 in
Length	39 in

Electrical Ratings

Rating - Indoor Amperage	2500
Rating - Outdoor Amperage	3000

Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30007941](#)
- [Specifications - B33G394NTN](#)