



## B34F32G1TN Flexible Copper Braid

By Burndy

Catalog # B34F32G1TN

Tin Plated Ferrules.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	B34F32G1TN
Connector Type	Braid
Material	Copper
UPC	621945454835

UPC 12 Digit 6219454548355

### Dimensions

Length	32 in
Width	4 in

### Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	

### Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	150

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50064228](#)
- [Specifications - B34F32G1TN](#)