



## B3D12G64TN Flexible Copper Braid

By Burndy  
Catalog # [B3D12G64TN](#)

Tin Plated Ferrules.



### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	3
Plated	Y
UPC	781810362198
UPC 12 Digit	7818103621988

### Dimensions

Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in
Length	12 in

### Electrical Ratings

Rating - Indoor Amperage	470
Rating - Outdoor Amperage	560

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 10039373-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-B3D12G64TN-SPEC-EN | REV 1/2024