



## B3D15D31G57W Flexible Copper Braid

By Burndy  
Catalog # [B3D15D31G57W](#)

Tin Plated Ferrules.



### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	3
Plated	Y
UPC	781810206164
UPC 12 Digit	7818102061644

### Dimensions

Dimension - Hole Size inch	0.44 in
Dimension - L Length Overall mm	389 mm
Dimension - Length Overall inch	15.31 in
Dimension - Pad Width inch	1.19 in
Length	15.31 in
Thickness	0.25 in

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-B3D15D31G57W-SPEC-EN | REV 5/2024