

B3D18 Flexible Copper Braid

By Burndy
Catalog # B3D18

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

| | |
|---------------------------------------|---------------|
| Catalog Number | B3D18 |
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 3 |
| Plated | N |
| UPC | 781810205648 |
| UPC 12 Digit | 7818102056488 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - Hole Size inch | 0.44 in |
| Dimension - L Length Overall mm | 457 mm |
| Dimension - Length Overall inch | 18.00 in |
| Dimension - Pad Width inch | 1.19 in |
| Dimension - Z (inch) | 2.62 in |
| Length | 18 in |
| Thickness | 0.25 in |

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50115865](#)
[Specifications - B3D18](#)