



B3E12N Flexible Copper Braid

By Burndy
Catalog # B3E12N

Cu Flexible Braid Jumper, 3 Braids in Ferrules, 2 Holes 2 Ferrules, 1.75" Spacing, 12.00" L, .56" Hole Dia., Amp Rating: 700(Indoor) 840(Outdoor).



General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	3
Plated	Y
UPC	781810005293
UPC 12 Digit	7818100052933

Dimensions

Dimension - D inch	3.00 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.64 in
Length	12 in

Electrical Ratings

Rating - Indoor Amperage	700
Rating - Outdoor Amperage	840

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_BD_Lineart](#)
[Sales Drawings - SE210201-02_DI](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-B3E12N-SPEC-EN | REV 5/2024