



B3F12D50NTN Flexible Copper Braid

By Burndy
Catalog # B3F12D50NTN

Tin Plated Ferrules.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	B3F12D50NTN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	3
Plated	Y
UPC	781810478547

Dimensions

Dimension - L Length Overall	318 mm
mm	
Dimension - Length Overall	12.50 in
inch	
Length	12.5 in

Electrical Ratings

Rating - Indoor Amperage	820
Rating - Outdoor Amperage	980

Certifications And Compliance

Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	15
Minimum Pack Quantity	128
Pallet Quantity	1350

Product Assets

- [3D Models - B3F12D50NTN_MODEL-PDF](#)
- [3D Models - B3F12D50NTN_MODEL-STEP](#)
- [3D Models - B3F12D50NTN_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10099257](#)
- [Specifications - B3F12D50NTN](#)