



## B3F18NTN Flexible Copper Braid

By Burndy  
Catalog # [B3F18NTN](#)

Tin Plated Ferrules.



### General

Catalog Number	B3F18NTN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	3
Plated	N
UPC	781810204955

### Dimensions

Dimension - L Length Overall mm	457 mm
Dimension - Length Overall inch	18.00 in
Length	18 in

### Electrical Ratings

Rating - Indoor Amperage	820
Rating - Outdoor Amperage	980

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Carton Quantity	8
Minimum Pack Quantity	1
Pallet Quantity	720

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE212301-01](#)
- [Specifications - B3F18NTN](#)