

B3F30G74 Flexible Copper Braid

By Burndy
Catalog # B3F30G74

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

| | |
|----------------|--------------|
| Catalog Number | B3F30G74 |
| Connector Type | Braid |
| Material | Copper |
| UPC | 621945452626 |

Dimensions

| | |
|------------------------------|-----|
| Dimension - L Length Overall | 762 |
| mm | |

| | |
|----------------------------|-------|
| Dimension - Length Overall | 30 |
| inch | |
| Length | 30 in |

Electrical Ratings

| | |
|---------------------------|-------|
| Rating - Indoor Amperage | 820 A |
| Rating - Outdoor Amperage | 980 A |

Certifications And Compliance

| | |
|------------------------------|----|
| Certification - CSA Approved | No |
| Standards - RoHS Compliance | CM |
| Status | |

Logistics

| | |
|-----------------------|----|
| Carton Quantity | 2 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 70 |

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50060438](#)
[Specifications - B3F30G74](#)