



B3G11N Flexible Copper Braid

By Burndy
Catalog # B3G11N

Flexible Copper Braid.



General

| | |
|----------------|--------|
| Catalog Number | B3G11N |
| Connector Type | Braid |
| Material | Copper |

Dimensions

| | |
|------------------------------------|-------|
| Dimension - L Length Overall mm | 279 |
| Dimension - Length Overall inch | 11 |
| Length | 11 in |

Electrical Ratings

| | |
|---------------------------|--------|
| Rating - Indoor Amperage | 960 A |
| Rating - Outdoor Amperage | 1150 A |

Certifications And Compliance

| | |
|------------------------------|-----|
| Certification - CSA Approved | No |
| Standards - RoHS Compliance | CM |
| Status | |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|-----|
| Carton Quantity | 10 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 900 |

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SE..212210-01](#)
[Specifications - B3G11N](#)