



## B3G12NSL Flexible Copper Braid

By Burndy  
Catalog # [B3G12NSL](#)

Flexible Copper Braid.



### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	3
Plated	Y
UPC	781810297681

### Dimensions

Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in
Length	12 in

### Electrical Ratings

Rating - Indoor Amperage	960
Rating - Outdoor Amperage	1150

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 10009619-01\\_C](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-B3G12NSL-SPEC-EN | REV 1/2024