



B3G19N Flexible Copper Braid

By Burndy
Catalog # [B3G19N](#)

Flexible Copper Braid.



General

Catalog Number	B3G19N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	3
Plated	Y
UPC	781810225950

Dimensions

Dimension - L Length Overall mm	483 mm
Dimension - Length Overall inch	19.00 in
Length	19 in

Electrical Ratings

Rating - Indoor Amperage	960
Rating - Outdoor Amperage	1150

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	4
Minimum Pack Quantity	4
Pallet Quantity	384

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE..212210-01](#)
- [Specifications - B3G19N](#)