

B3G30N Flexible Copper Braid

By Burndy
Catalog # B3G30N

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	B3G30N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	3
Plated	Y
UPC	781810294659

Dimensions

Dimension - L Length Overall	762 mm
mm	

Dimension - Length Overall	30.00 in
inch	
Length	30 in

Electrical Ratings

Rating - Indoor Amperage	960
Rating - Outdoor Amperage	1150

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	2
Minimum Pack Quantity	1
Pallet Quantity	120

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SE..212210-01](#)
[Specifications - B3G30N](#)