

## B3G72N Flexible Copper Braid

By Burndy  
Catalog # B3G72N



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	B3G72N
Connector Type	Braid
Material	Copper
Material - Ferrules	Copper
Physical Attribute - Number of Braids	3
Plated	Y
UPC	781810529799

### Dimensions

Dimension - L Length Overall	1829
mm	
Dimension - Length Overall	72
inch	
Length	72 in

### Electrical Ratings

Rating - Indoor Amperage	960 A
Rating - Outdoor Amperage	1150 A

### Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	UI
Status	

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - SE..212210-01](#)  
[Specifications - B3G72N](#)