



B42G31D604N Copper Braid 31.60"x4.00"x0.69"

By Burndy

Catalog # B42G31D604N

Copper Braid 31.60"x4.00"x0.69".



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	B42G31D604N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	8
UPC	781810373668
UPC 12 Digit	7818103736688

Dimensions

Dimension - L Length Overall mm	803 mm
Dimension - Length Overall inch	31.60 in
Dimension - Pad Width inch Length	4.00 in
Thickness	31.6 in
	0.69 in

Electrical Ratings

Amperage Rating	2 A
-----------------	-----

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	900

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - B42G31D604N](#)