



B45D17D19G1 Flexible Copper Braid

By Burndy

Catalog # B45D17D19G1

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

| | |
|---------------------------------------|--------------|
| Catalog Number | B45D17D19G1 |
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Copper |
| Physical Attribute - Number of Braids | 20 |
| Plated | Y |
| UPC | 621945449572 |

Dimensions

| | |
|------------------------------|----------|
| Dimension - L Length Overall | 437 |
| mm | |
| Dimension - Length Overall | 17.19 |
| inch | |
| Length | 17.19 in |
| Weight | 16.3 lb |

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------------|-----|
| Carton Quantity | 4 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 384 |

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50060357](#)
- [Specifications - B45D17D19G1](#)