

## B4D14N Flexible Copper Braid

By Burndy  
Catalog # B4D14N

Flexible Copper Braid.



### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810200056

### Dimensions

Dimension - L Length Overall mm	356 mm
Dimension - Length Overall inch	14.00 in
Length	14 in

### Electrical Ratings

Rating - Indoor Amperage	600
Rating - Outdoor Amperage	720

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	1200

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SE210201-03](#)