



## B4D18 Tinned Copper Braid 18"x1.19"x0.34"

By Burndy  
Catalog # B4D18

Tinned Copper Braid 18"x1.19"x0.34".



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	B4D18
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
Plating Type	Tin Plated
UPC	781810078280
UPC 12 Digit	7818100782800

### Dimensions

Dimension - Hole Size inch	0.44 in
Dimension - L Length Overall mm	457 mm
Dimension - Length Overall inch	18.00 in
Dimension - Pad Width inch Length	1.19 in
Thickness	0.32 in

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	2250

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - B4D18](#)