

B4E18G88TN Flexible Copper Braid

By Burndy

Catalog # B4E18G88TN

Tinned copper braid 12"x1.64"x0.38".



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	B4E18G88TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	4
UPC	621945457218
UPC 12 Digit	6219454572188

Dimensions

Dimension - Length Overall inch	12
Dimension - Width inch	1.64
Dimension - Width mm	42 mm
Length	18 in

Electrical Ratings

Rating - Indoor Amperage	850 A
Rating - Outdoor Amperage	1020 A

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	5
Minimum Pack Quantity	1
Pallet Quantity	480

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50066296](#)
[Specifications - B4E18G88TN](#)