



B4E25G82TN Flexible Copper Braid

By Burndy

Catalog # [B4E25G82TN](#)

Tin Plated Ferrules.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number B4E25G82TN

Connector Type	Braid
Material	Copper
UPC	781810351062
UPC 12 Digit	7818103510622

Dimensions

Length	25 in
--------	-------

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - B4E25G82TN](#)