



## B4E25G82TN Flexible Copper Braid

By Burndy

Catalog # [B4E25G82TN](#)



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number                      B4E25G82TN

|                |               |
|----------------|---------------|
| Connector Type | Braid         |
| Material       | Copper        |
| UPC            | 781810351062  |
| UPC 12 Digit   | 7818103510622 |

### Dimensions

|        |       |
|--------|-------|
| Length | 25 in |
|--------|-------|

### Certifications And Compliance

|                                    |    |
|------------------------------------|----|
| Standards - RoHS Compliance Status | EX |
|------------------------------------|----|

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - B4E25G82TN](#)



A Hubbell brand