



B4E51D60G42W Flexible Copper Braid

By Burndy
Catalog # B4E51D60G42W

Tin Plated Ferrules.

Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	B4E51D60G42W
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y



UPC	781810088456
UPC 12 Digit	7818100884566

Dimensions

Dimension - L Length Overall mm	1311 mm
Dimension - Length Overall inch	51.60 in
Length	51.6 in

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - sc076149-01](#)
[Specifications - B4E51D60G42W](#)