

B4EE38TNCG1 Flexible Copper Braid

By Burndy
Catalog # B4EE38TNCG1



Tin plated copper braid 38"x2.75"x0.54".

Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	B4EE38TNCG1
Connector Type	Braid
Material	Copper
Material - Ferrules	Copper
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810420997
UPC 12 Digit	7818104209977

Dimensions

Dimension - L Length Overall	965 mm
mm	
Dimension - Length Overall	38
inch	
Dimension - Width inch	2.75
Length	38 in
Weight	11.7 lb

Electrical Ratings

Amperage Rating	1500 A
Rating - Outdoor Amperage	1500

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	15
-----------------------	----

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - B4EE38TNCG1](#)