

## B4F12NTN Flexible Copper Braid

By Burndy  
Catalog # B4F12NTN

Tin Plated Ferrules.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	B4F12NTN
Connector Type	Braid
Material	Copper
Physical Attribute - Number of Braids	4
Plated	Y
UPC	621945448179

UPC 12 Digit 6219454481799

### Dimensions

Dimension - L Length Overall mm	305
Dimension - Length Overall inch	12
Length	12 in

### Electrical Ratings

Rating - Indoor Amperage	1000 A
Rating - Outdoor Amperage	1200 A

### Certifications And Compliance

Certification - CSA Approved Yes

### Logistics

Minimum Pack Quantity 1

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - SE212248-01](#)  
[Specifications - B4F12NTN](#)