



## B4F13G78TN Flexible Copper Braid

By Burndy

Catalog # [B4F13G78TN](#)

Tin Plated Ferrules.



### General

Catalog Number	B4F13G78TN
Connector Type	Braid
Material	Copper
UPC	781810474495
UPC 12 Digit	7818104744955

### Dimensions

Dimension - L Length Overall mm	330.2 mm
Dimension - Length Overall inch	13 in
Length	13 in

### Electrical Ratings

Rating - Indoor Amperage	1200 A
Rating - Outdoor Amperage	1000 A

### Certifications And Compliance

Standards - RoHS Compliance CM  
Status

### Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	900

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - B4F13G78TN](#)