



## B4F16D50NTN Flexible Copper Braid

By Burndy  
Catalog # [B4F16D50NTN](#)

Tin Plated Ferrules.



### General

Catalog Number	B4F16D50NTN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810206508
UPC 12 Digit	7818102065088

### Dimensions

Dimension - L Length Overall mm	419 mm
Dimension - Length Overall inch	16.50 in
Length	16.5 in

### Electrical Ratings

Rating - Indoor Amperage	1000
Rating - Outdoor Amperage	1200

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	540

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE212248-01](#)
- [Specifications - B4F16D50NTN](#)