



## B4F24 Flexible Copper Braid

By Burndy  
Catalog # B4F24

Flexible Copper Braid.



### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	N
UPC	781810201336
UPC 12 Digit	7818102013366

### Dimensions

Dimension - Hole Size inch	0.44 in
Dimension - L Length Overall mm	613 mm
Dimension - Length Overall inch	24.12 in
Dimension - Pad Width inch	1.44 in
Length	24 in
Thickness	0.88 in

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Minimum Pack Quantity	6
-----------------------	---

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-B4F24-SPEC-EN | REV 1/2024