



# B4F30N Flexible Copper Braid

By Burndy  
Catalog # [B4F30N](#)

Flexible Copper Braid.



### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810230893
UPC 12 Digit	7818102308933

### Dimensions

Dimension - L Length Overall mm	762 mm
Dimension - Length Overall inch	30.00 in
Length	30 in

### Electrical Ratings

Rating - Indoor Amperage	1000 A
Rating - Outdoor Amperage	1200 A

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	2250

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SE212248-01](#)



A proud member of the Hubbell Family.