



B4F44N Flexible Copper Braid

By Burndy
Catalog # [B4F44N](#)

Flexible Copper Braid.



General

Catalog Number	B4F44N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810219812
UPC 12 Digit	7818102198122

Dimensions

Dimension - L Length Overall mm	1118 mm
Dimension - Length Overall inch	44.00 in
Length	44 in

Electrical Ratings

Rating - Indoor Amperage	1000 A
Rating - Outdoor Amperage	1200 A

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	3
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE212248-01](#)
- [Specifications - B4F44N](#)