



B4G12NNK Flexible Copper Braid

By Burndy
Catalog # [B4G12NNK](#)

Nickel Plated Ferrules.



General

| | |
|---------------------------------------|---------------|
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 4 |
| Plated | Y |
| UPC | 781810257036 |
| UPC 12 Digit | 7818102570366 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 305 mm |
| Dimension - Length Overall inch | 12.00 in |
| Length | 12 in |

Electrical Ratings

| | |
|---------------------------|------|
| Rating - Indoor Amperage | 1200 |
| Rating - Outdoor Amperage | 1440 |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - se211997-01](#)



A proud member of the Hubbell Family.