

B4G20 Flexible Copper Braid

By Burndy
Catalog # B4G20

Flexible Copper Braid.



General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	N
UPC	781810432266
UPC 12 Digit	7818104322666

Dimensions

Dimension - Hole Size inch	0.44 in
Dimension - L Length Overall mm	508 mm
Dimension - Length Overall inch	20.00 in
Dimension - Pad Width inch	1.69 in
Dimension - Z inch	3.25 in
Length	20 in
Thickness	0.94 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	360

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)