



B4G20N Flexible Copper Braid

By Burndy
Catalog # [B4G20N](#)

Flexible Copper Braid.



General

Catalog Number	B4G20N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810204788
UPC 12 Digit	7818102047888

Dimensions

Dimension - L Length Overall mm	508 mm
Dimension - Length Overall inch	20.00 in
Length	20 in

Electrical Ratings

Rating - Indoor Amperage	1200
Rating - Outdoor Amperage	1440

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	3
Minimum Pack Quantity	1
Pallet Quantity	288

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - se211997-01](#)
- [Specifications - B4G20N](#)