



B4G24NSV Flexible Copper Braid

By Burndy
Catalog # [B4G24NSV](#)

Silver Plated Ferrules.



General

| | |
|---------------------------------------|---------------|
| Catalog Number | B4G24NSV |
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 4 |
| Plated | Y |
| UPC | 781810199954 |
| UPC 12 Digit | 7818101999544 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 610 mm |
| Dimension - Length Overall inch | 24.00 in |
| Length | 24 in |

Electrical Ratings

| | |
|---------------------------|------|
| Rating - Indoor Amperage | 1200 |
| Rating - Outdoor Amperage | 1440 |

Certifications And Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 25 |
|-----------------------|----|

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - se211997-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-B4G24NSV-SPEC-EN | REV 6/2024