



B4G47D3NTN Flexible Copper Braid

By Burndy
Catalog # [B4G47D3NTN](#)

Tin Plated Ferrules.



General

Catalog Number	B4G47D3NTN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810444658
UPC 12 Digit	7818104446588

Dimensions

Dimension - L Length Overall mm	1201 mm
Dimension - Length Overall inch	47.30 in
Length	47.3 in

Electrical Ratings

Rating - Indoor Amperage	1200
Rating - Outdoor Amperage	1440

Certifications And Compliance

Standards - RoHS Compliance Status	NC
------------------------------------	----

Logistics

Carton Quantity	12
Minimum Pack Quantity	1
Pallet Quantity	1080

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - se211997-01](#)
- [Specifications - B4G47D3NTN](#)